



# **Technical Data Sheet**

2450 **te**//or° Article:

Model: Assembly Gloves BLACK TOUCH®

Sizes: 5, 6, 7, 8, 9, 10, 11, 12

For details on product dimensions and weights see below (table).

Colour: grey/black

Other variants: 2452 = black/grey, with nitrile nubs Material: Carrier material: nylon/spandex

Coating: 100% nitrile

Mat. thickness: 0,8 mm (approx.) Packaging: 144 pair / carton Subpackaging: 12 pair, bundled

Details of packaging are below mentioned (table)

#### Care instructions:



Category II - includes mean risks not listed **PPE-category:** under Cat. I or III, according to Regulation

(EU) 2016/425, Annex I

(published in the Official Journal of the European

Union)

#### Standardize:

EN ISO 21420:2020 - Protective gloves - General requirements and test <u>methods</u>

EN 388:2016+A1:2018 - Protective gloves against mechanical risks



Abrasion resistance Cut resistance (Coupe test) Tear resistance 3 Puncture resistance Cut resistance (TDM) according to EN ISO 13997:1999 X

### EN 13594:2015 - Impact protection

Test result: X

EN 407:2020 - Protective gloves and other hand protective equipments against thermal risks (heat and/or fire)



Limited Flame Spread contact heat convective heat Radiant heat Small splashes of molten metal Large splashes of molten metal

EGV 1935:2004 - Regulation (EC) of the European Parliament and of the Council dated 27 October 2004 on materials and objects intended to come into contact with food and repealing Directives 80/590/EEC and 89/109/EEC, Official Journal of the European Union L 388/4 dated 13.11.2004 (and their changes)



The protective gloves can be used in the food industry as well as in private households for handling and processing food. They may be in direct contact with dry

food for short periods of time.

(X = not tested)



© BIG Arbeitsschutz GmbH













#### Fittings:

Nylon/spandex knit, nitrile coated palm (black), touchscreen ready, knitted cuff, material thickness palm: approx. 0,8 mm, approx. 15 gauges (= 1.449 mm).

Silicone-free. The claim 'silicone-free' refers to the materials used in production. No guarantee can be given for cross-contamination, for example during packaging or transport of the goods.

#### **Characteristics:**

Comfortable to wear and a secure grip, including when wet. Highly flexible and an excellent fit, highly elastic, therefore highly dexterous. Breathable. Silicone free. LABS conformity VDMA 24364

#### Application:

Applicable for general assembly work with medium risks and high requirements on the sense of touch (regarding mechanical risks), e.g. in the craft trade, construction sector, trade fair construction, automotive industry, mechanical engineering industry, food industry, agricultural sector

# Additional information regarding purpose, applications and risk assessment:

These product satisfy the requirements of the quoted standards. Please note that the actual conditions of use cannot be simulated and that the decision on the product's suitability for its intended purpose therefore lies exclusively with the user. The manufacturer is not responsible for improper use. Hence, an assessment of the residual risk should be performed before use in order to determine whether this product is suitable for its intended purpose. Kindly note the printed pictograms and performance levels.

#### Precautionary measures during use:

- These gloves must never be immersed in chemical substances or come into contact with chemical substances.
- Only use forearm-protection with a printed chemical pictogram when handling chemicals.
- Make certain that the selected forearm-protection is resistant to the chemicals being used.
- Do not use these forearm-protection to protect against serrated edges or blades, etc.
- If forearm-protection must be used in a hot environment, make certain that they satisfy the requirements of EN 407:2020 and that they were tested as specified therein.
- Do not use the forearm-protection close to moving machine parts.
- Check the gloves carefully before use to make certain there are no defects or imperfections.
- It is reasonable to assume that the forearm-protection also protect against sharp objects such as injection needles, provided they satisfy the requirements of perforation resistance according to EN 388:2016+A1:2018.
- Discard damaged, worn, dirty or soiled forearm-protection, irrespective of the substance (including on the inside), as they may lead to skin irritation and rashes. Consult a doctor or dermatologist should such cases arise.

# EN ISO 21420:2020 - Protective gloves - General requirements and test methods:

This standard specifies the relevant test methods to be used for all protective gloves and the general requirements for design principles, glove assembly, resistance of the glove material to water penetration, harmlessness, comfort and performance as well as the labeling to be carried out by the manufacturer and the information to be provided by the manufacturer.

# EN 388:2016+A1:2018 - Protective gloves against mechanical risks:

Protective gloves against mechanical risks must achieve at least Level 1 or Level A in at least one of the properties (abrasion, cut, tear and puncture resistance) of the TDM cut resistance test according to EN ISO 13997:1999.

Abrasion resistance: The number of abrasion cycles required to rub through the test specimen.

Cut resistance (Coupe-Test): The number of test cycles in which the test specimen is cut through with constant force and repeated contact.

Tear resistance: The force needed to continue tearing the cut sample.

Puncture resistance: The force needed to puncture the sample using a standardized test stylus.

Cut resistance (TDM): The minimum force that is necessary to cut through the test specimen with a single contact.

### EN 388:2016+A1:2018



Test criteria	Rating	Article 2450
A = Abrasion resistance	0 - 4	4
B = Cut resistance (Coupe test)	0 - 5	1
C = Tear resistance	0 - 4	3
D = Puncture resistance	0 - 4	1
E = Cut resistance (TDM) according to EN ISO 13997:1999	A - F	X
F = Impact protection test according to EN 13594:2015	P	X

The higher the test number, the better the test performance. X means 'not tested'. P means 'passed'.

Test	1	2	3	4	5
A = Abrasion resistance (number of abrasion cycles)	100	500	2000	8000	-
B = Cut resistance (index) Coupe test	1,2	2,5	5,0	10,0	20,0
C = Tear resistance (N)	10	25	50	75	-
D = Puncture resistance (N)	20	60	100	150	-











Test	Α	В	С	D	E	F
E = Cut resistance according to EN ISO 13997:1999 (N)	2	5	10	15	22	30
Article 2450						

# EN 13594:2015 - Impact protection:

Every area specified as providing protection against impact must be tested. The test method (dimensions of the test sample) does not permit impact testing of the finger protection. Gloves to protect against mechanical risks may be designed and manufactured in such a way that they offer specific impact damping (e.g. impact protection on the knuckles. the back of the hand, the palms). These gloves must satisfy the requirements of Level 1 according to EN 13594:2015.

The results of the Coupe test must only be taken as indications if blunting occurs during the cut resistance test (B), while the TDM cut resistance test (E) provides reference results in regard to performance.

#### WARNING:

The overall classification for gloves with two or more layers does not necessarily indicate the performance of the outermost layer. Gloves with mechanical resistance that achieve and demonstrate Level 1 tear resistance (C) or higher must not be worn if there is a risk of them catching when operating machines with moving parts.

The tests refer to the palm of the gloves.

407:2020 - Protective gloves and other hand protective equipments against thermal risks (heat and/or fire)



test criteria	Possible ratings	Article 2450
A =Limited Flame Spread	0 - 4	X
B =contact heat	0 - 4	1
C = convective heat	0 - 4	X
D = Radiant heat	0 - 4	X
E = Small splashes of molten metal	0 - 4	X
F = Large splashes of molten metal	0 - 4	X

Die Kennzeichnung ,X' anstelle einer Zahl bedeutet, dass die Handschuhe nicht für die Verwendung, die von dieser Prüfung abgedeckt ist, vorgesehen sind

Test	Test result according to EN407	1	2	3	4
Limited Flame Spread:	Burn time (s)	≤15	≤10	≤3	≤2
	Glow time (s)	-	≤120	≤25	≤5
Contact heat:	Contact temperature °C	100	250	350	500
	Threshold time (s)	≥15	≥15	≥15	≥15
Convective heat:	Heat transfer index HTI (s)	≥4	≥7	≥10	≥18
Radiant heat:	Heat transfer t24 (s)t24 (s)	≥7	≥20	≥50	≥95
Small splashes of molten metal:	Number of splashes	≥10	≥15	≥25	≥35
Large splashes of molten metal:	Molten iron (g)	30	60	120	200

# WARNING:

The glove must not come into contact with an open flame if it has not been tested or achieved at least performance level 1 in the limited flame spread test.

The levels only apply to the entire product and all of its layers for gloves comprising several separable layers.

#### Foodstuffs test report



The glove fulfils the requirements of Regulation (EC) No. 1935/2004, Sections 30 and 31 of the German Food and Feed Code (LFGB) and the German Commodities Ordinance (Bedarfsgegenständeverordnung) in their current versions.

The gloves are only suitable for contact with dry foodstuffs. Detailed information on this can be found in the Declaration of Conformity for contact with food.

The test report with the number (25424)072-570465 was issued by: Bureau Veritas Consumer Products Services Germany GmbH Wilhelm-Hennemann-Str. 8 19061 Schwerin Deutschland

# Markings on the gloves:

Trademark, art.-no. of manufacutrer, size, CE-icon, pictograms with the corresponding numbers of the relevant European PPE standards, i-mark, factory icon with date of manufacture: month/year, hourglass pictogramm with expiry date: month/year













te<mark>)∵(o</mark>r 2450 Brand label of manufacturer Article no. of the manufacturer

10

Size of gloves according to EN ISO 21420:2020 (example)





Pictograms with the corresponding numbers of the relevant European PPE standards (example, detailed pictogram see previous



The glass and fork symbol testifies that the product complies with the applicable requirements of Regulation (EC) 1935:2004 (and subsequent amendments) and can be used in the preparation and handling of foodstuffs.



The CE marking confirms compliance with the requirements of European Regulation 2016/425.



i mark: Reference to the manufacturer's information.



Date of manufacture month/year: 00/0000



Expiry date month/year: 00/0000

# **Dimensions/weights article:**

Size	Length in cm	Width in cm	material thickness palm	Weight in g/pair
5	22,00	8,00	0,08	27
6	22,00	8,00	0,08	27
7	23,00	8,00	0,08	34
8	24,00	9,00	0,08	40
9	25,00	9,50	0,08	41
10	26,00	10,00	0,08	42
11	27,00	10,50	0,08	46
12	22,00	8,00	0,08	27

The above values are approximate and subject to slight variations.

# Details of packaging unit:

Size	kg gross	kg net	Length in cm	Width in cm	Height in cm
5	5,50	4,50	42	24	31
6	5,50	4,50	42	24	31
7	5,90	4,80	42	24	31
8	6,00	5,00	42	24	31
9	6,50	5,50	43	28	31
10	7,60	6,60	43	28	31
11	7,90	6,90	44	29	31
12	5,50	4,50	42	24	31

The above values are approximate and subject to slight variations.

# Hazardous ingredients - REACH (Registration, Evaluation, Authorization and Restriction of Chemicals):

The product is manufactured in compliance with Annex XVII of the European REACH regulation 1907/2006 and contains no hazardous substances in concentrations requiring declaration.













#### **Declaration of Conformity**

CE

These products are classified as personal protective equipment (PPE). The CE mark confirms that the product satisfies the applicable requirements of Regulation (EU) 2016/425.

#### Identification and selection:

Selection of model must be made according to workplace requirements, type of hazard and relevant environmental conditions. The employer is responsible for choosing the right PSA. Therefore, it is necessary to check the suitability of the product for the needs needed before use.


#### Regulation for use:

The product fulfil the safety requirements only if they are worn in an entirely correct manner and in their best condition. Check the product for defects or flaws before use. If any tears or holes appear during use of the product, they must be disposed of immediately. Make sure that the product are not too large or too small and fit exactly. Modifications to this PPE are not permitted. Follow the instructions provided in the manufacturer's information and keep this information in a safe place during the entire service life of the PPE. We assume no responsibility for any damages and/or consequences resulting from improper use.

# **Care instructions:**











Do not wash and bleach the gloves. Drying in tumbler is not possible. Do not iron. Professional dry and wet cleaning is not allowed.

Both new and used gloves must be checked carefully for any damage before they are worn. Never store dirty gloves if they are intended for reuse. Users are advised to carefully remove the gloves on the right and then the left if it is not possible to remove the soiling or if doing so would present a danger. Here, use the hand wearing the glove in such a way that the other glove can be removed without coming into contact with the soiling.

#### Storage and aging:

The product should be stored in their original packaging in a dark, cool and dry place, away from direct sunlight and away from any sources of heat. Prolonged contact with direct sunlight or excessive heat will shorten the service life. Avoid any contact of the product with solvents which could result in changes to the product or its properties. The service life is generally up to 5 years when used and stored properly (see also expiry date on the packaging). The product are also marked with the production date (month/year).

Used products may be contaminated with environmentally harmful or hazardous substances. Dispose of in accordance with applicable local laws.

Allergies, caused by the proper use of the products, are not yet known. If an allergic reaction still occurs, consult a doctor or dermatologist.

#### First Aid:

Remove the product if they are contaminated with hazardous materials. In case of contact with skin: immediately consult a doctor if an allergic reaction occurs. In case of eye contact: wash out the affected eye with water. Consult a doctor immediately.

# The notified body responsible for the EU Type Examination:

Parc Scientifique Tony Garnier 4 rue Hermann Frenkel 69367 Lyon Cedex 07 Frankreich Kenn-Nr.: 0075

> For the full Declaration of Conformity and manufacturer's information, please visit: www.big-arbeitsschutz.de



issued on 14.12.2023/Rev.03









